




REVISIONS				
P/F	LTR	DESCRIPTION	DATE	APPROVED
✓	✓	G REV-REDWAI	5-2-83	MS/RH
		CB2-515		

1. FOR USE WITH: RG-16/U, 179/U, 187/U CABLE.
2. CRIMPING TOOL: 69245-1.
3. SEE I.S. 1799-3.



ITEM	QTY	DESCRIPTION	PART NO
7	1	FERRULE	328666
6	1	GASKET	2-329106-1
5	1	LOCK WASHER	329632
4	1	JAM NUT	329631
3	1	GASKET	329633
2	1	CRIMP END ASSY	50793-5
1	1	JACK ASSY, BHD	329800

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS ± .010
ANGLES ± .010

MATERIAL

FINISH

CONTRACT NO

DR *M. E. Smith* 5-3-83CHK *S. S. Heide* 9/8/83APPD *M. E. Smith* 12/1/83APPD *M. E. Smith* 12/1/83

DSGN APPD

OTHER APPD

AMPAMP INCORPORATED
Harrisburg, Pa. 17105NAME **CONNECTOR, COAXIAL, RF
JACK, BHD, SERIES BNC**

SIZE

A

FSCM NO

00779

DRAWING NO

2-329458-1SCALE **NTS**

SHEET