


SWITCH-BASIC

CATALOG LISTING
DT-2RV22-A7



4-40 UNC X .125 REF ROUND HEAD
SCREW AND LOCKWASHER (6)

NOTE -
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 9-14 OZ
RELEASE FORCE ----- 3 OZ MIN
DIFFERENTIAL TRAVEL ----- .195-.305
OVERTRAVEL ----- .031 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
D P D T

UL LISTED-FILE E12252
CODE L59
10A-125 OR 250 VAC
0.3A-125 VDC; 0.15A-250 VDC



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .085 LB

DT-2RV22-A7

DRAWING
NUMBER

813

ISSUE

813

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

REVISIONS

A	CO17725	L E B	11 JUNE 63
B	CO24941	M B S	2 DEC 68
C	CO28075	M B S	26 AUG 69
D	CO37528	C J H	31 AUG 76
E	CO38280	TSK	17 JUL 87
F	CO61634	CO	75204-B
G	75204-B	S A V	1 FEB 94