



DESCRIPTION: 97 SERIES SOLDER STYLE PANEL & CABLE MOUNT  
D-SUB CONNECTORS

MODEL NUMBER: 40-97XXS

APPLICATION: FOR CABLE

CRIMP TOOL: N/A


IMPEDANCE: N/A

FREQUENCY RANGE: 0-15 MHz

MATERIAL: HOUSING STEEL NICKEL PLATED  
INSULATOR PBT+FIBER-GLASS UL94-V0 WHITE  
CONTACT COPPER-ALLOY, GOLD PLATED

RoHS COMPLIANCE: YES

TECHNICAL DETAIL: N/A



**DIM OUTLINE**

MODEL NUMBER	PIN	A	B	C	D
40-9709S	09	30.80	24.99	16.30	19.20
40-9715S	15	39.15	33.32	24.65	27.70
40-9725S	25	53.00	47.04	38.40	41.10
40-9737S	37	69.30	63.50	54.80	57.30

	3RD ANGLE PROJECTION 	<b>AIM-Cambridge</b>	
	RoHS <input checked="" type="checkbox"/> 2002/95/EC	Title: D-Sub Connector, 97 Series, Solder Style Panel and Cable Mount, Female	
<small>           This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be tracked or copied without permission and is returnable upon demand.         </small>		Model No. <b>40-97XXS</b>	
<small>           UNLESS OTHERWISE SPECIFIED            UNITS: METRIC            .XX ± .51            .XXX ± .127            ANGLES ± 2°         </small>	Size <b>A</b>	DO NOT SCALE DRAWING	Date: <b>9/9/2013</b>
<small>           INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.         </small>		Sheet 1 of 1	

5e144200094aed  
752020000001194  
09  
2013.09.09  
11:50:10 +0800