


LTR	DESCRIPTION	DATE	BY
-	Released	2/5/02	JCL



I. MATERIALS & FINISHES

center contact: Silver (50u") Plated Brass
 outer contact: Silver (50 u") Plated Brass
 body: Silver (50 u") Plated Brass
 backnut: Nickel (50 u") Plated Copper
 dielectric: Teflon® PTFE
 gaskets: Nitrile Rubber
 attachment: braid clamp

II. ELECTRICAL PROPERTIES

impedance: 50 ohms
 working voltage: 1000 vrms (max)
 vswr: 1.15:1 (max) up to 3 GHz
 insertion loss: 0.10 x $\sqrt{f}$ ghz

Unless otherwise specified, dimensions are in inches. Tolerances are applicable when specified.

These drawings and specifications contain proprietary information which is the property of Times Microwave Systems.

Approvals

Drawn	JCL	2/5/02



TIMES MICROWAVE SYSTEMS

Wallingford, CT 06492
 (203) 949-8400; (203) 949-8423.Fax
 www.timesmicrowave.com

EZ-1200-NFC-PL

Type-N male (plug) – Non-Solder Pin
 for LMR-1200-LLPL Cable

Size A	CAGE CODE 68999	Drawing No.: 3190-912
--------	-----------------	-----------------------

Scale: NA

Rev. (-)

Sheet: 1 of 1