

**Mallory Sonalert Products, Inc.**

Part #:

SBT5TMFL**Sales Outline Drawing**


Revision:

C**Specifications:****cUL Recognized to IEC60601-1-8 AMD1
Temp/Energy Delivery Melody - Medium Priority Only**

Sound Level Category:	Loud
Mode of Operation:	Medium Priority Alarm - 3 beeps repeating every 7.5 sec
Voltage Rating:	3.3 to 5 VDC
Frequency:	150 to 4000 Hz
Loudness @ 10cm:	85 to 95 dB(A) Typ.
Average Current Draw:	<35mA Typ.
Ipk Current*:	300mA
Housing Material:	ABS 777D Plastic Resin, Black
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight Typical:	0.6 oz (17g)
Options:	Please contact factory.

Dimensions: Inches (mm)**cUL Recognized****ROHS Compliant**

PATENT NUMBER: 7880593



*Ipk = Instantaneous Peak

tolerances:

 ± 0.01 [± 0.3] ± 0.005 [± 0.1]