





		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	ECR-21-119335	25JUN2022	TL	HL



4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PACKAGE 2	108-60121	30 u "	45.0	8.0	44.5	91	70	73.15	89	71.65	164	7-2337939-4
PACKAGE 1		30 u "	86.5		44.5	91	70	73.15	89	71.65	164	5-2337939-8
PACKAGE 4		30 u "	53.5		28	58	37	40.15	56	38.65	98	5-2337939-7
PACKAGE 3		30 u "	36.5		19.5	41	20	23.15	39	21.65	64	5-2337939-6
NA		30 u "	22.5		12.5	27	6	9.15	25	7.65	36	5-2337939-5
PACKAGE 1		30 u "	10.0		44.5	91	70	73.15	89	71.65	164	5-2337939-4
PACKAGE 4		30 u "	10.0		28	58	37	40.15	56	38.65	98	5-2337939-3
PACKAGE 3		30 u "	10.0		19.5	41	20	23.15	39	21.65	64	5-2337939-2
NA		30 u "	10.0		12.5	27	6	9.15	25	7.65	36	5-2337939-1
PACKAGE 1		108-60121-1	15 u "		86.5	44.5	91	70	73.15	89	71.65	164
PACKAGE 4	15 u "		53.5		28	58	37	40.15	56	38.65	98	4-2337939-7
PACKAGE 3	15 u "		36.5		19.5	41	20	23.15	39	21.65	64	4-2337939-6
NA	15 u "		22.5		12.5	27	6	9.15	25	7.65	36	4-2337939-5
PACKAGE 1	15 u "		10.0		44.5	91	70	73.15	89	71.65	164	4-2337939-4
PACKAGE 4	15 u "		10.0		28	58	37	40.15	56	38.65	98	4-2337939-3
PACKAGE 3	15 u "		10.0		19.5	41	20	23.15	39	21.65	64	4-2337939-2
NA	15 u "		10.0		12.5	27	6	9.15	25	7.65	36	4-2337939-1
PACKAGE 1	G/F		86.5		44.5	91	70	73.15	89	71.65	164	3-2337939-8
PACKAGE 4	G/F		53.5		28	58	37	40.15	56	38.65	98	3-2337939-7
PACKAGE 3	G/F	36.5	19.5		41	20	23.15	39	21.65	64	3-2337939-6	
NA	G/F	22.5	12.5	27	6	9.15	25	7.65	36	3-2337939-5		
PACKAGE 1	G/F	10.0	44.5	91	70	73.15	89	71.65	164	3-2337939-4		
PACKAGE 4	G/F	10.0	28	58	37	40.15	56	38.65	98	3-2337939-3		
PACKAGE 3	G/F	10.0	19.5	41	20	23.15	39	21.65	64	3-2337939-2		
NA	G/F	10.0	12.5	27	6	9.15	25	7.65	36	3-2337939-1		
PACKAGE 2	108-60121	30 u "	NA	44.5	91	70	73.15	89	71.65	164	2-2337939-5	
PACKAGE 1		30 u "	NA	44.5	91	70	73.15	89	71.65	164	2-2337939-4	
PACKAGE 4		30 u "	NA	28	58	37	40.15	56	38.65	98	2-2337939-3	
PACKAGE 3		30 u "	NA	19.5	41	20	23.15	39	21.65	64	2-2337939-2	
NA		30 u "	NA	12.5	27	6	9.15	25	7.65	36	2-2337939-1	
PACKAGE 1	108-60121-1	15 u "	NA	44.5	91	70	73.15	89	71.65	164	6-2337939-4	
PACKAGE 4		15 u "	NA	28	58	37	40.15	56	38.65	98	6-2337939-3	
PACKAGE 3		15 u "	NA	19.5	41	20	23.15	39	21.65	64	6-2337939-2	
NA		15 u "	NA	12.5	27	6	9.15	25	7.65	36	6-2337939-1	
PACKAGE 1		G/F	NA	44.5	91	70	73.15	89	71.65	164	2337939-4	
PACKAGE 4		G/F	NA	28	58	37	40.15	56	38.65	98	2337939-3	
PACKAGE 3		G/F	NA	19.5	41	20	23.15	39	21.65	64	2337939-2	
NA		G/F	NA	12.5	27	6	9.15	25	7.65	36	2337939-1	
PACKING SPEC	PRODUCT SPEC	GOLD PLATING	W	V	J	D	N	C	B	A	POS.	PART NUMBER
			MYLAR SIZE (PAGE 4)									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ±-

ANGLES ±-

FINISH -

MATERIAL

-

-

DWN FRED LIU 12JUN2018

CHK HOPE LU 12JUN2018

APVD HOPE LU 12JUN2018

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME PCI EXPRESS CARD EDGE CONNECTOR

GEN4 , STANDARD VERSION

SIZE A2

CAGE CODE 00779

DRAWING NO C-2337939


RESTRICTED TO -

SCALE 3:1

SHEET 2 OF 6

REV F

1471-9 (3/13)



4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FRONT VIEW

REAR VIEW

36POS AS SHOWN

FRONT VIEW

REAR VIEW

64POS AS SHOWN

FRONT VIEW

REAR VIEW

98POS AS SHOWN

FRONT VIEW

REAR VIEW

164POS AS SHOWN

W

REF

V

REF

J

MYLAR SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ±

ANGLES ±

FINISH ±

MATERIAL

-

-

DWN
FRED LIU
12JUN2018

CHK
HOPE LU
12JUN2018

APVD
HOPE LU
12JUN2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR

GEN4 , STANDARD VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2337939

-

F

SCALE

3:1

SHEET

4

OF

6

REV

F

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A


A



PACKAGE 1



PACKAGE 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU 12JUN2018	 TE Connectivity			
DIMENSIONS:		CHK HOPE LU 12JUN2018				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HOPE LU 12JUN2018	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN4 , STANDARD VERSION			
	0 PLC ±- 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ±- ANGLES ±- FINISH	PRODUCT SPEC APPLICATION SPEC WEIGHT				
MATERIAL	-	CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779	DRAWING NO C-2337939	RESTRICTED TO -
-	-		SCALE 3:1	SHEET 5 OF 6	REV F	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A


A



PACKAGE 3



PACKAGE 4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU 12JUN2018	 TE Connectivity			
DIMENSIONS:		CHK HOPE LU 12JUN2018				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HOPE LU 12JUN2018	NAME PCI EXPRESS CARD EDGE CONNECTOR			
	0 PLC ±-	PRODUCT SPEC	GEN4 , STANDARD VERSION			
	1 PLC ±0.3	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	2 PLC ±0.20	APPLICATION SPEC	A2	00779	C-2337939	-
	3 PLC ±0.050	-	CUSTOMER DRAWING			
MATERIAL	4 PLC ±-	WEIGHT	SCALE 3:1			
-	FINISH	-	SHEET 6 OF 6			
-	-	-	REV F			