

1 2 3 4



SCALA NON RIPRODUCIBILE
(DO NOT SCALE)

DIMENSIONI IN mm

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

THIRD ANGLE PROJECTION



1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1

OBSOLETE

STAGNATO
(TIN PLATED)

OTTONE
(BRASS)

280201-2

(LIN PLATED)

OTTONE
(BRASS)

280201-1

FINITURA / COLORE
(FINISH / COLOUR)

MATERIALE
(MATERIAL)

NUMERO
(PART NUMBER)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED

RELEASE FOR PUBLICATION

18

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHT
RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES UNLESS OTHERWISE
SPECIFIED)

± 0,3

ANGOLI
(ANGLES) ± 2°

DIAM. ISOLANTE
(INS. DIA. RANGE)

4.0 mm DIA. MAX.

RANGO FILO
(WIRE RANGE)

1-2.5 mm²

SCALA
(SCALE)

AMP

AMP ITALIA S.p.A.
Corso F.lli Cervi, 15
COLLEGNO (TORINO)

DESCRIZIONE
(DESCRIPTION)

SQUARE TONGUE WITH
INSULATION SUPPORT. (STRIP FORM)

LOC.

SIZE

NUMERO
(DWG NO.)

1A4 C-280201

REV.

P1

FOGLIO
(SHEET)

1 OF 1

P1 ECO-09-026346

KK

NOV09

P Revised ET00-0067-01

GS

09/02/01

N REVISED AND REDRAWN
(ET00-0293-97) C. L. T.

18.7

01

REV. REVISIONI
(REVISION RECORD)

DIS. DATA
(DR) (DATE)

APP. (APP.)