


CONTACT CONFIGURATION  
TIMING (BBM) NON-SHORTING

## NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC  
350MILLIAMP, 110VAC/DC
6. TIMING: NON-SHORTING
7. OPERATING FORCE 0.8±0.3 kg-cm
8. OPERATING TEMP: -30°C TO 85°C
- ▲9. CIRCUIT SP: 3 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL.
- ▲11. HARDWARE SUPPLIED ON SWITCH:  
LOCKWASHER, HEXNUT, LOCK RING
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



TITLE KC43D0.001NPS

|     |        |                         |          |    |
|-----|--------|-------------------------|----------|----|
| A   | 21719  | RELEASED FOR PRODUCTION | 11/14/14 | rc |
| REV | PCR NO | DESCRIPTION             | DATE     | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |            |    |         |     |
|-------|------------|----|---------|-----|
| SCALE | DATE       | DR | DWG     | REV |
| 1.5:1 | 11/14/2014 | rc | G510284 | A   |