

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	CPN 17-CUST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	-------------	-----------	----	------------------	-----------



Description: N-male 3 pc crimp RG8X
Part No: CPN17
Application: For RG8X Cable
Crimp Tool: 24-312
Impedance: 50 Ohms
Frequency Range: 0-11 GHz
Material: Crimp Sleeve Brass Nickel plated
Contact Brass Ni/Au plated
Body Brass Nickel plated
Coupling Nut Brass Nickel plated
RoHS Compliance: Yes
Technical Detail: Refer to Emerson Document P/N 26-0000

DRAWING NO.




CPN17-CUST

REVISIONS

01	OFFICAL RELEASE				<i>Betty</i>
	08-17-09	J	T	T	

200000
8085338
40801

CUSTOMER COPY

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
		JEAN.JIN	08-17-09
DECIMALS	mm	CHECKED BY	DATE
X	± 0.5	TERRY.W	08-17-09
X.X	± 0.2	APPROVED BY	DATE
X.XX	± 0.1	THOMAS	08-17-09
ANGLES	± 0.5°	U/M	mm



THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

Connectivity
SolutionsTITLE
N-MALE 3 PC CRIMP RG8XSHEET
1 OF 1DRAWING NO.
CPN17-CUSTSIZE
A