




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
BD	48						
			F1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



CABLE CLAMP HOUSING

BLANK GATE

1. PARTS PACKAGED UNASSEMBLED.
2. CABLE GATES ARE INTERCHANGEABLE ALLOWING 90° & 180° CABLE EXIT.
- 3 COMPONENTS INDIVIDUALLY BULK PACKED AND SHIPPED AS A UNIT PACKAGE KIT.




TEXTURED FINISH


SELF-TAPPING SCREW
SEE TABLE

CABLE GATE


SIZE 3 CONNECTOR
FOR REF ONLY




3-A
.195 DIA
CABLE REF




3-B
.360 DIA
CABLE REF



3-C
.215 DIA
CABLE REF




3-D
BLANK
GATE



3-E
.390 DIA
CABLE REF

GATES

OBSOLETE OBSOLETE	SLOTTED	3	207345-4
	SLOTTED	AS SHOWN	207345-3
	CROSS-RECESSED	3	207345-2
	CROSS-RECESSED	AS SHOWN	207345-1
SCREW VERSION		PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 9-16-86	 TE Connectivity				
DIMENSIONS: INCHES		CHK C. RICHARD 9-16-86					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APVD S. SCHUFERLY 9-16-86	NAME CABLE CLAMP KIT, SIZE 3, ONE PIECE, 90DEG & 180DEG EXIT, AMPLIMITE®				
		PRODUCT SPEC —					
		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT —	A2	00779	C-207345		
		MATERIAL MOLDED PARTS: POLYPROPYLENE, COLOR: BLACK SCREWS: STEEL PER ASTM A108	FINISH SCREWS: ZINC PHOSPHATE PER MIL-P-16232	CUSTOMER DRAWING			SCALE NTS