

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-11-023039			21FEB12	KH	MS

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-2, BLACK.
TERMINAL: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC AND CHROMATE PLATED.

ELECTRICAL:
MAXIMUM CURRENT: 20A.
OPERATING VOLTAGE: 600V.
WIRE RANGE: 12 AWG MAX.

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C



- 1

WHITE INK MARKING, APPROX AS SHOWN.
- 2

NICKEL PLATED BRASS SCREW.
- 3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 4

ALL SCREWS BOTTOMED, TORQUE 2 TO 4 IN-LBS



SEE FIGURE 3

OBSOLETE	7.562	17	SSB7FP170201	1-1546972-7
	7.125	16	SSB7FP16020111	9-796602-4
2	7.125	16	SSB7FP160201	1-1546972-6
	6.687	15	SSB7FP150201	4-1437416-6
2	6.250	14	SSB7FP140203	1546561-4
	6.250	14	SSB7FP140201	4-1437416-5
2	5.812	13	SSB7FP130201	4-1437416-3
	5.375	12	SSB7FP120201	4-1437416-0
2	4.937	11	SSB7FP110201	1-1546972-1
	4.500	10	SSB7FP100203	3-1437416-6
2	4.500	10	SSB7FP100201	3-1437416-4
	4.062	9	SSB7FP090203	1-1546561-9
2	4.062	9	SSB7FP090201	1546972-9
	3.625	8	SSB7FP08020111	1986330-3
2	3.625	8	SSB7FP080203	2-1437416-9
	3.625	8	SSB7FP080201	1546972-8
2	3.187	7	SSB7FP070203	2-1437416-6
	3.187	7	SSB7FP07020111	2-1437416-5
2	3.187	7	SSB7FP070201	2-1437416-4
	2.750	6	SSB7FP06020111	1986330-2
2	2.750	6	SSB7FP060203	2-1437416-3
	2.750	6	SSB7FP060201	2-1437416-1
2	2.312	5	SSB7FP050203	2-1546972-7
	2.312	5	SSB7FP050201	1-1437416-5
2	1.875	4	SSB7FP04020111	1986330-1
	1.875	4	SSB7FP040203	1-1437416-3
2	1.875	4	SSB7FP040201	1-1437416-1
	1.437	3	SSB7FP030201	1437416-6
2	1.000	2	SSB7FP020201	1437416-2
	DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± .02

3 PLC ± .010

4 PLC ± -

ANGLES ± 1°

FINISH -

DWN S SCHLGEL 2/10/05

CHK S YODER 2/10/05

APVD S YODER 2/10/05

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

SSB7FPXX0201

SIZE A3

CAGE CODE 00779

DRAWING NO C-9-796602-2

RESTRICTED TO -

SCALE NTS

SHEET 1 OF 2

REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

2

3

4

5

6

7

2-1437416-5

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

9-796602-4

1

2

3

4

5

6

7

8

1986330-3

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

1986330-5

1

2

3

4

1986330-1

1

2

3

4

5

6

1986330-2

2

11.937

27

SSB7FP270201

9-796602-2

11.500

26

SSB7FP260203

1-1546561-8

11.500

26

SSB7FP260201

2-1546972-6

11.062

25

SSB7FP250201

2-1546972-5

10.625

24

SSB7FP24020111

1986330-5

10.625

24

SSB7FP240201

2-1546972-4

10.187

23

SSB7FP230201

2-1546972-3

9.750

22

SSB7FP220201

2-1546972-2

9.312

21

SSB7FP210201

2-1546972-1

8.875

20

SSB7FP200201

2-1546972-0

8.437

19

SSB7FP190201

1-1546972-9

8.000

18

SSB7FP180201

1-1546972-8

DIM A

NO. OF POS.

CATALOG NUMBER

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0

1

2

3

4

PLC

± -

± -

± .02

± .010

± -

ANGLES

± 1°

0

1

2

3

4

PLC

± -

± -

± .02

± .010

± -

FINISH

-

DWN

S SCHL GEL

2/10/05

CHK

S YODER

2/10/05

APVD

S YODER

2/10/05

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

SSB7FPXX0201

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-9-796602-2

-

SCALE

SHEET

REV

NTS

2 OF 2

A

1470-19

(3/11)