



赤色被覆
RED INS.

SERATION
エレ-シ

(表参照) (SEE TAB.)
被覆外径 INS. DIA.



(P/N)	(STUD)	(H DIA)	(INS. DIA)
型番	スタッド	H-J法	被覆外径
171506-1	#8	4.34	2.03~3.18
-2	#10	5.00	2.03~3.18
-3	#8	4.34	2.67~3.56
-4	#10	5.00	2.67~3.56
-5	#12	5.66	2.03~3.18
-6	特別	5.79	2.67~3.56
-7	5mm		2.3~3.18
-8	5mm	5.00	2.67~3.56

(F) OBSOLETE
(E) OBSOLETE
(E) OBSOLETE
(F) OBSOLETE
(F) OBSOLETE

E Change Applicable Body Y.O N.Y 23JAN17 F OBSOLETE Y.O N.Y 14APR17

D1 OBSOLETE (REV. 05) F.N 47 6-16-93

D REVISED (REV. B) P-DWG 2-4-45 6-16-93

C REVISED (REV. B) S.O 4-1 1/4/72

E ADDED MARK H.S 4/1 8/1/75

A REVISED (REV. B) H.S 4/1 7/1/75

O 1/1 1/1/75

LTR 変更 (REVISION RECORD) DR CHK DATE

DR 1/1 1/1/75

CHK 1/1 1/1/75

参考図面
(CUSTOMER COPY
REFERENCE ONLY)

TE

TE Connectivity

有先銅

銅メッキ

0.26 ~ 1.04 mm AWG22-18

表 参考

1/1 1/1/75

1/1 1/1/75

1/1 1/1/75

1/1 1/1/75

1/1 1/1/75

1/1 1/1/75

丸型端子 RING TERMINAL

JAC-171506 F