



- NOTES: UNLESS OTHERWISE SPECIFIED
 1. FOR USE WITH .085", .086" CABLE OR EQUIVALENT.
2. MATERIAL SPECIFICATIONS:
 RETAINING RING: BERYLLIUM COPPER
 INSULATOR: PTFE
 ALL OTHER METAL PARTS: BRASS
3. FINISH SPECIFICATIONS:
 CONTACT: .000003 MIN GOLD OVER .000050 MIN NICKEL
 ALL OTHER METAL PARTS: THIN GOLD OVER .000050 MIN NICKEL
4. ELECTRICAL SPECIFICATIONS:
 IMPEDANCE: 50 OHMS
 FREQUENCY RANGE: DC - 6.0 GHz
5. CONTACT SHIPPED LOOSE.
6. SOLDER CONTACT.



CATALOG P/N: 1320A204-405

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] .XXX [XXX] ± .005 [0.13] .XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 8:1				 by WINCHESTER Winchester Electronics Corporation 159 Park Road Ext Suite 104 Middlebury, Connecticut 06762				
CUSTOMER SALES DRAWING				THIRD ANGLE 		MMCX STRAIGHT DIRECT SOLDER PLUG (FOR .085", .086")		
DRAWN	DATE	APPROVED	DATE	A	SD1320A204-405	SHT	OF	REV
J	09/08/2016	J	09/13/2016					
APPROVED	DATE	APPROVED	DATE					
DCAM	09/08/16	XXX	XX/XX/XX					