




REV. 0

DCO 142639

GROUND PIN


COIL: @ 25°C
 RESISTANCE _____ 1560 OHMS $\pm 10\%$
 NOMINAL VOLTAGE _____ 26.5 VDC
 MUST OPERATE _____ 14.2 VDC
 MUST RELEASE _____ 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX
 RELEASE TIME 1.5 MS MAX
 CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 1A 28 VDC RESISTIVE 100,000
 OPERATIONS

DR. PBB 1/18/01

CK.

CI Technologies
 advanced control electronic solutions

CUST. _____ QPL
 CUST. NO. M39016/9-104P REV. _____

JMA RELAY

JMACG-26XPS