




5			4					
PART NUMBER	ITEM ① BODY	ITEM ② CONTACT	ITEM ③ INSULATOR	ITEM ④ CRIMP SLEEVE	ITEM ⑤ CUPLING NUT			
27-9104	BRASS NICKEL PLATED	BRASS GOLD PLATED	DELTRIN	BRASS NICKEL PLATED	ZINC NICKEL PLATED			

DRAWING NO. 27-9104									
REVISIONS									
01	OFFICIAL RELEASE							2009.09	
	08-18-09	L	L	T	H			Betty	08 09.34.35 +08'00



受控 CONTROLLED DOCUMENT				
编号 P/N	27-9104	版本 Rev	01	日期 Rel'd Date
SEP 14,09				



NOTES:

- 1. IMPEDANCE: 50 OHMS NOMINAL
- 2. FREQUENCY RANGE: 0-4 GHz
- 3. CABLE ACCEPTABILITY:BELDEN 8281
- 4. CABLE RETENTION: 20 lbs MIN
- 5. RECOMMENDED TEMPERATURE RANGE: -55 °C TO +85°C
- 6. FURTHER TECHNICAL DETAIL: REFER TO EMERSON DOCUMENT P/N 27-0000

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY LINDA.WU	DATE 08-18-09
DECIMALS	mm	CHECKED BY LINDA.WU	DATE 08-18-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-18-09
X.X	± 0.2	U/M	mm
X.XX	± 0.1		
ANGLES	± 0.5°		

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 EMERSON Network Power		Connectivity Solutions	
TITLE BNC 3PC CRIMP FOR 8281			
SHEET 1 OF 1	DRAWING NO. 27-9104		SIZE C

THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1994
COMPANY CONFIDENTIAL