







SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
2-1, 5-4	2-3, 5-6

(ON) = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN mm [INCH]
2. GENERAL TOLERANCE: x.x = ±0.4
x.xx = ±0.25
3. TERMINAL NUMBERS FOR REF. ONLY
- ▲ 4. CONTACT RATING: 0.1A @ 30 VDC
5. TRAVEL: FULL = 1.8mm
- ▲ 6. OPERATING FORCE: 200±80gf
7. ELECTRICAL LIFE: 10,000 CYCLES
8. CONTACT RESISTANCE: 30mΩ MAX.
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER
11. 2002/95/EC (RoHS) COMPLIANT



B	21131	Re-Release Part Number	5/16/13	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE JN2UOANAGX

SCALE 3:1

DATE 5/16/2013

DR rc

DWG P200000

REV B