



NUMBER C-173977

三 角 法 (3rd ANGLE PROJECTION)

METRIC

単位: ㎜ DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



注記;

- 適用電線範囲: AWG# 28-26 (UL1571, UL1061)
被覆外径: 0.83-1.05
- 材料: ハウジング-ガラス入PBT UL94V-0
コンタクト-銅合金
- 運用製品規格番号: 108-5218
- 取付運用規格番号: 114-5104

NOTES;

- APPLICABLE WIRE SIZE: AWG# 28-26 (UL1571, UL1061)
INSULATION DIA RANGE: 0.83-1.05
- MATERIAL:
HOUSING: PBT (G.F) UL94V-0
CONTACT: COPPER ALLOY
- PRODUCT SPEC: 108-5218
- APPLICATION SPEC: 114-5104

7-173977-5	5-173977-5	3-173977-5	1-173977-5	15	28	30.8	32
7- ↑ -4	5- ↑ -4	3- ↑ -4	1- ↑ -4	14	26	28.8	30
7- -3	5- -3	3- -3	1- -3	13	24	26.8	28
7- -2	5- -2	3- -2	1- -2	12	22	24.8	26
7- -1	5- -1	3- -1	1- -1	11	20	22.8	24
7- -0	5- -0	3- -0	1- -0	10	18	20.8	22
6- -9	4- -9	2- -9	-9	9	16	18.8	20
6- -8	4- -8	2- -8	-8	8	14	16.8	18
6- -7	4- -7	2- -7	-7	7	12	14.8	16
6- -6	4- -6	2- -6	-6	6	10	12.8	14
6- -5	4- -5	2- -5	-5	5	8	10.8	12
6- -4	4- -4	2- -4	-4	4	6	8.8	10
6- -3	4- -3	2- -3	-3	3	-AS SHOWN 図示-		
6-173977-2	4-173977-2	2-173977-2	173977-2	2	-AS SHOWN 図示-		

BLACK 黒色	CREAM YELLOW クリームイエロー	LIGHT BLUE ライトブルー	NATURAL 自然色	POS 極数	A	B	C
-------------	--------------------------	----------------------	----------------	-----------	---	---	---

PART No.
製品型番

TE TE Connectivity

適合電線断面積 (WIRE RANGE) NOTE 1 mm ² (AWG -)		被覆外径 (INSULATION DIA.) NOTE 1 mmφ		名称 (NAME) MT REC HOUSING ASS'Y (AMP CT CONNECTOR 2mm PITCH)			
材料 (MATERIAL) NOTE 2		仕上 (FINISH)		一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10を超え 30以下: ±0.25 30を超え 100以下: ±0.3 角 度: ±3°			
DR. 23/AUG/99 J. TSUJI	DE. 23/AUG/99 J. Tsuji	APP. 25/AUG/99 J. Tsuji		SIZE A3	LOC J	番号 (No.) C-173977	
LTR 変更 (REVISION RECORD)		DR. CHK. DATE		尺 度 (SCALE) 4-1		REV. G3	SHEET 1 OF 1

(CUSTOMER DRAWING)

参 考 図 面