


SPECIFICATIONS:

CONTACT RATING: 3A @ 125 VAC OR 28 VDC (RESISTIVE)
 INITIAL CONTACT RESISTANCE: 20 MILLIOHMS MAXIMUM
 INSULATION RESISTANCE: 1000 MEGOHMS MINIMUM @ 500 VDC.
 DIELECTRIC STRENGTH: 1000 VOLTS RMS AT SEA LEVEL
 LIFE EXPECTANCY: 10,000 CYCLES AT FULL RATED LOAD
 CONTACTS: SOLID SILVER
 SEAL-TOGGLE: PER MIL-S-83731A
 STATIC: PARAGRAPH 4.8.20
 DYNAMIC: PARAGRAPH 4.8.20


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
D	0G3C-0194-05	27MAR07	MZ



TTE23P-8T 1/4	2 TO 1 5 TO 4	OFF	2 TO 3 5 TO 6
TTF23N-8T 1/4	2 TO 1 5 TO 4	NONE	2 TO 3 5 TO 6
TTF13F-8T 1/4	2 TO 1	OFF	2 TO 3
TTF13D-8T 1/4	2 TO 1	NONE	2 TO 3
SWITCH NO.	FLAT	FLAT	FLAT

TERMINALS CONNECTED WHEN TOGGLE IS IN POSITION SHWN
 NOTE: TERMINAL DESIGNATION NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON SWITCHES NO'S 4, 5, 6 FOR D.P. VERSION ONLY.

AUGAT D/N 40210



DISTRIBUTION									
1	2	3	4	5	6	7	8	9	10

INSPECT PER ALCO QAS 100	
SYMBOL	A.Q.L.
□	CRITICAL
△	MAJOR
NONE	MINOR

UNLESS OTHERWISE SPECIFIED	
DIMENSIONS ARE IN INCHES TOLERANCES ON: 3 PL. DECIMALS ± .010 ANGLES ± .1° FRACTIONS	
SURF	✓
SIGNATURES	DATE
DRAWN	7/2/07
CHECKED	7/2/07
ENGRG	5/1/07
ISSUED	

tyco Electronics	
CUSTOMER DRAWING - TOGGLE SWITCH	
SEALED SP & DP TTE13(*)-8T 1/4	
SIZE: SC. NO.	DWG. NO.
CL	1437563-6
SCALE 4/1	SHEET OF 1