

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		ECO-21-006943	13OCT2021	RK	MZ

D

C

B



A

D

C

B

A



1. THIS CONNECTOR WILL ACCEPT TWO TYPE I, SIZE 12 SOCKET CONTACTS AND EIGHT MULTIMATE SOCKET CONTACTS.
 2. TYPE I CONTACTS MATE FIRST, BREAK LAST.
 3. MAX WIRE INSULATION USED WITH THIS RECEPTACLE IS 2.67[.105] DIA FOR MULTIMATE SOCKET CONTACTS.
4. TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

213128

213128-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 05/18/95	TE Connectivity			
DIMENSIONS: mm[INCHES]		CHK R.STONE 5-23-95				
		APVD A.FRANTUM 5-25-95	NAME RECEPTACLE, ARR 17-10M, REVERSE SEX, SERIES 4, CLASS A, SQUARE FLANGE, CPC			
		PRODUCT SPEC	SIZE A2			
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	CAGE CODE 00779			
MATERIAL NYLON, BLACK		FINISH -	DRAWING NO C-213128			
		WEIGHT -	RESTRICTED TO -			
		CUSTOMER DRAWING	SCALE 2:1			
			SHEET 1 OF 1			
			REV B			