



THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.
© COPYRIGHT - TE Connectivity Ltd.

REVISIONS			
P	LTR	DESCRIPTION	DATE
	C	ECO-21-005577	06MAY2021 RK MZ



- 1 THIS PLUG WILL ACCEPT 2 TYPE I, SIZE 12 PIN CONTACTS AND 8 MULTIMATE PIN CONTACTS
- 2 MAXIMUM WIRE INSULATION ACCEPTED BY THIS PLUG IS Ø2.67[Ø.105] FOR MULTIMATE PIN CONTACTS
- 3 WHITE STRIPE INDICATES MAJOR KEYWAY
- 4 WHITE DOT INDICATES MAJOR KEYWAY
- 5 TE LOGO LOCATED ANYWHERE ON THIS SURFACE

4	213130-3
3	213130-2
-	213130-1
KEYWAY MARKING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON CHK R.STONE	11/03/89 11-8-89
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	M.KAPEZYNSKI PRODUCT SPEC	NAME
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	± - ± - ± 0.13 [.005] ± - ± - ± -	11-8-89 — — — — —	PLUG, CPC, ARRANGEMENT 17-10M, REVERSE SEX, SERIES 4, CLASS A
MATERIAL UL 94V-0 RATED, NYLON BLACK	FINISH	WEIGHT	SIZE CAGE CODE DRAWING NO A2 00779 C-213130
			RESTRICTED TO —
			CUSTOMER DRAWING
			SCALE 4:1 SHEET 1 OF 1 REV C