

4

3



2

1

LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED (ECR-14-014356), ADD STD OFF	24NOV14	SC	HL

NOTES:




1. MATERIAL:
HOUSING: PBT WITH 30% GF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHIELD: PHOSPHOR BRONZE.
2. FINISH:
CONTACTS: GOLD FLASH OVER
0.762µm [30µ"] MIN. PALLADIUM-NICKEL PLATED ON CONTACT AREA,
2.54µm [100µ"] MIN. MATTE-TIN ON SOLDER TAIL, WITH
ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATED, WITH
2.54µm [100µ"] MIN. Cu UNDERPLATED OVERALL.
3. WAVE SOLDER CAPABLE TO 265°C PER TE TEST SPEC.
109-202, CONDITION B.



3.30	1-1734775-1
2.45	1734775-1
DIM A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 22MAY2007	TE Connectivity			
		CHK S. HOU 22MAY2007				
		APVD W.J. KE 22MAY2007	NAME			
		PRODUCT SPEC 108-57322	USB CONNECTOR, RECEPTACLE, FLAG, R/A, DIP, A TYPE			
		APPLICATION SPEC				
		WEIGHT 2.4 GRAMS	SIZE A3	CAGE CODE 00779	DRAWING NO C=1734775	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE -	SHEET 1 OF 2	REV C	

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
		SEE SHEET 1.				



11.1 Kg	10.1 Kg	100	21	2	4200 PCS
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /INNER BOX	INNER BOX /CARTON	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: mm		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				
MATERIAL		PRODUCT SPEC	NAME			
FINISH		APPLICATION SPEC	USB CONNECTOR, RECEPTACLE, FLAG, R/A, DIP, A TYPE			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		CUSTOMER DRAWING	A3	00779	C=1734775	—
		SCALE	SHEET		REV	
		—	2 OF 2		C	