

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

PROJECT

PRJ-16-000909157

PART NO.

X-2308341-X

DESCRIPTION

FULL METAL HOODS SIZE 2

CUSTOMER

GENERAL MARKET

REVISIONS

| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | A1  | REVISED PER ECR-16-013123 | 19SEP2016 | KK  | GG   |

1-2308341-3

29

39,5

12

15

33,3

42

2,2

12,8

d

50

45°

24

35,7

25

24,3

25

Case

25

24,3

36

Case

25

24,3

36

2-2308341-1

50

45°

24

35,7

25

24,3

25

Case

25

24,3

36

Case

25

24,3

36

NOTES:

1. FINISH:  
1-2308341-1 TO 2-2308341-2- CASE RAW  
2-2308341-3 TO 3-2308341-4 - CASE NICKEL-PLATED

2. LOCKING SCREWS: NICKEL-PLATED  
OTHER SCREWS: ZINC-PLATED

3. TEMPERATURE RANGE: -40°C TO +90°C

4. CABLE DIAMETER WITH EXTERNAL DIAMETER CABLE CLAMP: 4-14 mm.

5. STRAND DIAMETER OF CRIMP FLANGE: 2.7-8.7 mm.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

DIN ISO 2768-m

DIN 16901 130B

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

-

±

-

±

-

±

-

WEIGHT

-

CUSTOMER DRAWING

SCALE

NTS

SHEET

1 OF 2

REV

A1

DWN

KIRAN K

02AUG2016

CHK

GUNASEKHAR G

02AUG2016

APVD

GUNASEKHAR G

02AUG2016

NAME

FULL METAL HOODS SIZE 2

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=2308341

RESTRICTED TO

-

TE Connectivity

1471-9

(1/15)

