

G 25/10.0A/M RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

General ordering data

Version	Active components, Fuse
Order No.	0193100000
Type	G 25/10.0A/M RT
GTIN (EAN)	4008190023799
Qty.	10 pc(s).

G 25/10.0A/M RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	1.3 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Cartridge fuse	G-Si. 5 x 25	Characteristics	medium time-lag
Colour	Light Grey	Colour of the indicator	red
Current	10 A	Melting integral	370 A ² s
Optical function display	Yes	Power output (@ 1.5 In)	3.2 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	150 mV		

Rating data

Rated voltage	250 V	Rated current	10 A
---------------	-------	---------------	------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	