








SIGN	DATE	DESCRIPTION	APPROVER
△	01/08`14	Add the safety certification icon	Chen Bo
△			
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item (a) Male contact pin-01: Copper, Tin plated
- Item (b) Male contact pin-02: Copper, Tin plated
- Item (c) Terminal(housing): Thermoplastic (UL 94V-0)

- Electrical:
- Voltage rating: 300V
 - Current rating: 20A
 - Withstanding Voltage: 1.6 KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec

△ Safety Approval: cULus

- Critical dimension: △

EU 02 70 x 1 xxxx G

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EU 5.0 Series 2P (Left)				
PART NO.	EU0270x1xxxxG			DWG NO.	8EU0029	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Chen Bo 01/08`14	Chen Bo 07/30`12			Tolerance
						X. ±0.50
				SHEET: 01/01		X.X ±0.30
						X.XX ±0.10
				REV.: C		X° ±1°