



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	ECR-19-004071	03DEC2021	E.Z	N.S


リール引出し方向
DIRECTION OFF TOP OF REEL





VIEW W
テープ幅 32mm以上に適用
APPLIED TAPE WIDTH 32MM,MORE.



VIEW W
テープ幅 12mm, 16mm, 24mm に適用
APPLIED TAPE WIDTH 12MM, 16MM AND 24MM.



DETAIL X



50 POCKETS
空部 400mm 程度
WITHOUT CHARGE APPROX

製品装填部
WITH PRODUCT CHARGE

30 POCKETS MIN
空部 240mm MIN
WITHOUT CHARGE MIN

△ GENERAL TOLERANCE
10 ≥ ±0.2
30 ≥ >10: ±0.25
100 ≥ >30: ±0.3
ANGLES: ±3°

△ DIM. 28.4 AND DETAIL "X" APPLIED
TAPE WIDE, 32mm MORE.

△ 一般公差
10以下: ±0.2
10を越え 30以下: ±0.25
30を越え 100以下: ±0.3
角 度: ±3°

△ 28.4寸法及び"X" 詳細図は、
テープ幅 32mm以上に適用

OBSOLETE	AVAILABLE	0.115g	30.4	24.4	17.2	24	—	11.5	3500	61	2-2040832-6
	AVAILABLE	0.098g	30.4	24.4	14.7	24	—	11.5	3500	51	2-2040832-1
	AVAILABLE	0.087g	30.4	24.4	13.2	24	—	11.5	3500	45	1-2040832-8
	AVAILABLE	0.080g	30.4	24.4	12.2	24	—	11.5	3500	41	1-2040832-6
	AVAILABLE	0.074g	30.4	24.4	11.2	24	—	11.5	3500	37	1-2040832-4
OBSOLETE	AVAILABLE	0.053g	22.4	16.4	8.2	16	—	7.5	3500	25	2040832-8
STATUS		CONNECTOR WEIGHT	F	E	D	C	B	A	数量(ヶ) QTY/REEL	POS.(N)	EMBOSS TAPE PACKAGING PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL 材料	FINISH 仕上

DWN Y.KODAIRA 17NOV2008	CHK A.KUBO 26NOV2008
APVD T.KUSUHARA 26NOV2008	NAME 名称
PRODUCT SPEC 製品規格 108-78650	SIZE A3
APPLICATION SPEC 取付適用規格 411-78338	CAGE CODE 00779
WEIGHT	DRAWING NO 番号 C-2040832

TE Connectivity Ltd.

0.25FPC BF-L-1.3H
1.3mmH, 3.2mmW, GOLD PLATE

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
尺度 NTS

SHEET
1 OF 2

REV
F

