





PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	DCN 52377	03/23	SEE PDM



MATERIAL:

BODY, INSERT, CLAMP NUT, FERRULE, CONTACT & HEX NUT:	BERYLLIUM COPPER
INSULATOR:	PTFE
O-RING:	SILICONE RUBBER
LOCKWASHER:	PHOSPHOR BRONZE

FINISH:

BODY, INSERT, CLAMP NUT, HEX NUT, FERRULE CONTACT & LOCKWASHER:	GOLD OVER COPPER
---	------------------

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 18.0 GHz.
MAGNETIC FIELD STRENGTH:	<.1 mG

RECOMMENDED MOUNTING HOLE

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$
-----------	-----------	--