

5

4

3

2

1





D

C




B

A


Hood lower part




Hood upper part



Strain relief 1



Strain relief 2



Flathead screws

Mod.	Dat.	Name	Detail.	Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub hoods 25 poles not shielded	Maßstab/ Scale 1:1
EC01696	20/04/10	SC	Insp.	27/02/03	SH			
34793	09/01/08	PK	Stand.				TB 09 67 025 0571	Blatt/ Page 1 / 1
33806	26/09/06	PK						
31392	27/02/03	SH						
			HARTING EURL F-95972 Paris			Sub.		