







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	THE OFFICIAL VERSION RELEASED	14MAY2019	R.Z	S.L




SPECIFICATION:

1. CURRENT RATING: 1.5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



15U"	2340901-3
30U"	2340901-2
G/F	2340901-1
GOLD PLATING THICKNESS	TEPN

6	SHELL	STAINLESS STEEL	NI Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± 0.30
2 PLC ± 0.20
3 PLC ± 0.15
4 PLC ± —
ANGLES ± 3°
FINISH —

DWN
RAMBO ZHANG
22JAN2019

CHK
RICHARD MA
22JAN2019

APVD
SIMON LI
22JAN2019

PRODUCT SPEC

APPLICATION SPEC

WEIGHT
—

TE Connectivity

NAME
USB TYPE C 2.0 CONN REC MID-MOUNT
ONE ROW SMT TYPE WITH 0.035mm OFFSET

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2340901

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 2

REV
A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




COPYRIGHT — TE Connectivity Ltd.





ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



SEE DETAIL X



	REEL	CARTON
CONNECTOR (PCS)	1500	15000

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22JAN2019

RAMBO ZHANG

CHK 22JAN2019

RICHARD MA

APVD 22JAN2019

SIMON LI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING



TE Connectivity

NAME


USB TYPE C 2.0 CONN REC MID-MOUNT
ONE ROW SMT TYPE WITH 0.035mm OFFSET

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2340901	—

SCALE 1:1

SHEET 2 OF 2

REV A

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

MATERIAL

—

FINISH

—