




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4202-004.
TUSONIX RoHS COMPLIANT PART NUMBER: 4202-004 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART NO.: 60/40 SOLDER PLATED.
RoHS PART NO.: SILVER PLATED.
- PART MARKING: STANDARD BLACK INK FOR VARIATION AND DATE CODE. RoHS PART: GREEN FOR VARIATION AND DATE CODE.
- SUPPLIED WITH SILVER PLATED MOUNTING HEX NUT AND LOCK WASHER.

GMV CAP. (pF)	WORKING VOLTAGE (VDC)		CURRENT (Idc)	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
2500	500	350	15A	10 G Ω	1200	5	50	70	70

X-2015 Rev-0	REVISION RECORD				--TOLERANCES-- Unless Otherwise Specified	Title BUSHING STYLE EMI FILTER			
	0	Original Release C.O.	4202-004S WAS SK 6764-000 S L.E. 01-13-84	1					
		C.O. 1965	WORKING VOLTAGE REV'D -85 WAS -55 & 350 ADDED L.E. 3-3-91	2					
		C.O. 5800	RDN TO COMP FMT & METRIC ADDED L.E. 08-31-01	3					
		20010830-1-01	ADDED NOTES 1-3, DWV & I.R. S.M. 04-12-05	4		Drawn L.E. 08-30-01			
		20050407-6-02			DECIMAL ± .031 [0.79]	Approved T.C. 08-30-01			
					ANGLES ±	Scale 3 X			
					TUSONIX TUCSON, ARIZONA	A			
						4202-004			