






ITEM #	PART #	QTY	DESCRIPTION
1	TJS-102-1	1	SHELL HALF, RIBBED
2	TJS-102-3	1	JACK ASSEMBLY
3	TP-102-20	1	CRIMP, SLEEVE ($\varnothing$.39 X .20)
4	TJS-102-2	1	SHELL, HALF - SMOOTH
5	TJ-106-13	2	#4 WASHER, LOCK
6	TJ-106-14	2	NUT, #4-40 SPECIAL
7	TJS-102-15	2	SCREW

NOTES:
1) EACHPART SHALL BE MARKED WITH U-94A/U & M9177/5-2
2) PART SHALL BE ON QUALIFIED PRODUCT LIST FOR MIL-C-9177/5A
3) CRIMPING TOOLS USE M22520/S-01 HAND TOOL W/CRIMP DIE M22520/5-29, M22520/5-3S OR M22520/5-5S
4) MATING CONNECTORS M9177/1-1, & M9177/2-1

C TJS-102NSC



RECOMMENDED CABLE:
WM085/U (5-COND)
FOR USE WITH U-94A/U

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

						DWN.BY IDH		DATE 7/15/85		MATERIAL							
						CHECKED BY RWF		DATE 7/16/85		FINISH							
						APPR.BY		DATE		WEIGHT		SCALE = 1.00 :1					
										UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES & OR (mm)				TITLE CONNECTOR AUDIO AIRBORNE JACK, NO CLIP, 4 CONTACT, NO SWITCH			
										TOLERANCES:				SIZE		DWG. NO.	
										DECIMAL:				C		TJS-102NSC	
										FRACTION: ±XXX/XXX							
										ANGLES: ±X ° ±X'							
B	ADD: BOM: EXPLODED VIEW			12/3 2014	HR	±.XX(X.X) ±.XXX(X.XX) ±.XXXX(X.XXX) ±.0(X.0) ±.00(X.0X) ±.000(X.00X)											
LET.	REVISION			CN #	DATE	CHK	FRACTION: ±XXX ± X/XX		ANGLES: ±X ° ±X'		DO NOT SCALE DWG.		SHEET 1 OF 1				