

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN
(DIMENSIONS IN) mm

METRIC



PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

NOTES:

- 1 FOR USE ON STANDARD APPLICATORS
(RIGHT-LEFT FEED).
- 2 FOR USE ON MINIATURE APPLICATORS
(LEFT-RIGHT FEED;
AMP-O-MATOR APPLICATION).
- 3 DIFFERENT SHAPE FOR LOCKING LANCE
TE AMP ITALY PRODUCTION
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

SEZIONE A-A
(SECTION A-A)

SEZIONE B-B
(SECTION B-B)



4 OBSOLETE	3 2 1	STAGNATO (TIN PLATED)	OTTONE (BRASS)	1-160366-2	AR
	1	ARGENTATO (SILVER PLATED)	BRONZO FOSFOROSO (PHOS. BRONZE)	0-160366-6	AR
4 OBSOLETE	2 1	STAGNATO (TIN PLATED)	BRONZO FOSFOROSO (PHOS. BRONZE)	0-160366-5	AR
	1	NUDO (UNPLATED)	BRONZO FOSFOROSO (PHOS. BRONZE)	0-160366-4	AR
4 OBSOLETE	1	ARGENTATO (SILVER PLATED)	OTTONE (BRASS)	0-160366-3	AR
	2 1	STAGNATO (TIN PLATED)	OTTONE (BRASS)	0-160366-2	AR
	1	NUDO (UNPLATED)	OTTONE (BRASS)	0-160366-1	AR
NOTE		FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)	REV.

STATO DI FORNITURA - SCALA 1:1
(SUPPLY CONDITION - SCALE 1:1)

SENSO DI USCITA
DEL TERMINALE
DALLA BOBINA

(DIRECTION OFF
TOP OF REEL)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE) mm²

SCALA
(SCALE)

± 0.3
ANGOLI
(ANGLES) ± 2°

TE Connectivity

DIS. H. YAALI
(DR.) 24 JUN 99

DESCRIZIONE
(DESCRIPTION) FASTIN-FASTON® Connector

CONT. C. TARTARI
(CHK) 24 JUN 99

.110" sr. REC. CONTACT

AR5	REVISED PER ECO-11-005140	RK	31MAR99
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	APP. DATA (APP.) (DATE)

LOC. SIZE	NUMERO (DWG NO)	REV.	FOGLIO (SHEET)
I A3	C-160366	AR5	1 OF 1