

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-10-013614			13OCT10	HMR	CR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN OVER COPPER ALLOY.
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.

ELECTRICAL:
RATED CURRENT UL/CSA:
CLASS C: 20A, 300V
CLASS D: 5A, 600V
WIRE RANGE: 12-22 AWG

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX.


1 MARK WITH PERMANENT INK.



SEE FIGURE

SEE FIGURE
SEE FIGURE
SEE FIGURE
SEE FIGURE

9.000	9.314	23	JC6-P208-23	6-796985-5
8.625	8.939	22	JC6-P208-22-224	1776344-1
8.625	8.939	22	JC6-P208-22	6-796985-4
8.250	8.564	21	JC6-P208-21	6-796985-3
7.875	8.189	20	JC6-P208-20	6-796985-2
7.500	7.814	19	JC6-P208-19	6-796985-1
7.125	7.439	18	JC6-P208-18	2-796985-0
6.750	7.064	17	JC6-P208-17	6-796985-0
6.375	6.689	16	JC6-P208-16	5-796985-9
6.000	6.314	15	JC6-P208-15	1-796985-9
5.625	5.939	14	JC6-P208-14	5-796985-8
5.250	5.564	13	JC6-P208-13	5-796985-7
4.875	5.189	12	JC6-P208-12	5-796985-6
4.500	4.814	11	JC6-P208-11	5-796985-5
4.125	4.439	10	JC6-P208-10	5-796985-4
3.750	4.064	9	JC6-P208-09	4-1437665-6
3.375	3.689	8	JC6-P208-08	5-796985-3
3.000	3.314	7	JC6-P208-07	5-796985-2
2.625	2.939	6	JC6-P208-06	4-1437665-5
2.250	2.564	5	JC6-P208-05	4-1437665-4
1.875	2.189	4	JC6-P208-04-505	1776344-3
1.875	2.189	4	JC6-P208-04-504	1776344-2
1.875	2.189	4	JC6-P208-04-503	9-796985-7
1.875	2.189	4	JC6-P208-04-500	9-796985-6
1.875	2.189	4	JC6-P208-04	4-1437665-3
1.500	1.814	3	JC6-P208-03-172	1-796985-8
1.500	1.814	3	JC6-P208-03	4-1437665-2
1.125	1.439	2	JC6-P208-02	4-1437665-1
DIM. "B"	DIM. "A"	NO. OF POS.	CATALOG PART NO.	PART NUMBER












THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 5/7/03		 Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105	
DIMENSIONS: INCHES		CHK S. YODER 5/7/03			
		APVD S. YODER 5/7/03		NAME JC6-P208-XX ASSEMBLY	
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		WEIGHT —			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ± — 1 PLC ± — 2 PLC ± .01 3 PLC ± — 4 PLC ± — ANGLES ± —		SIZE A3	
MATERIAL —		FINISH —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-4-1437665-1	
				RESTRICTED TO —	
				SCALE NTS	
				SHEET 1 OF 2	
				REV D	

4

3

2

1



9-796985-7

1776344-2

9-796985-6

1776344-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 5/7/03	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK S. YODER 5/7/03				
		APVD S. YODER 5/7/03				
	0 PLC ± — 1 PLC ± — 2 PLC ± .01 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC	NAME			
		APPLICATION SPEC	JC6-P208-XX ASSEMBLY			
MATERIAL —	FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-4-1437665-1	RESTRICTED TO —
		CUSTOMER DRAWING	SCALE NTS	SHEET 2	OF 2	REV D