






LOC	DIST	REVISIONS					
H	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G4	REV PER ECR-10-000455	07JAN2010	JY	SY
			H	ECR-10-018652	10SEP10	SW	MQW
			J	ECR-12-010544	6NOV12	SY	AC

NOTES:

- ① MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL SHIELDING; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
UL-RATING 94V0.
 - ② GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
 - ③ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
 - ④ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - ⑤ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
 - ⑥ PLATING SHIELD:
CONTACT AREA : 0,76μm Au MIN.
ACTION PIN : 0,5μm SnPb MIN.
REMAINDER : Ni
 - ⑦ ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
 - ⑧ HOLE PATTERN FOR FEMALE CONNECTOR TYPE M
55 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - ⑨ ROW "r" 6 PLATED THROUGH HOLES FOR UPPERSHIELD
 - ⑩ SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
 - ⑪ AREA RESERVED FOR KEYING PART (BASIC P.N. 100526)
 - ⑫ CONTACT CAVITIES (3x) SUITABLE FOR 4,8 DIA. HIGH CURRENT,
HIGH FREQUENCY OR FIBRE OPTIC CONTACTS AS PER DIN 41626
(SEE ALSO NOTE 6).
 - ⑬ 1,3 DIA. PLATED-THROUGH HOLES (15x) CAN BE OMITTED
IF SPECIAL CONTACTS WITH CABLE CONNECTION OR FIBRE
OPTIC CONTACTS ARE USED.
 - ⑭ THIS ROW OF 11 CAVITIES (B1 TO B11) FOR
CONNECTOR ASSEMBLY PURPOSE ONLY.
 - ⑮ NOT PLATED-THROUGH HOLES (3x).
 - 16 FITS WITH LOWERSHIELD BASIC P/N 352112
 - ⑰ 0,76μm MIN GOLD PLATING AT MATING SURFACES.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	20JAN97
D. TRUBEN	

D. TRÖREN	
CHK	—

—	
APVD	—

PRODUCT SPEC

108-19082

APPLICATION SPEC

114-19029

WEIGHT	—
--------	---

CUSTOMER DRAWING

 Tyco Electronics Corporation

lyco Electronics

NAME	
------	--

Z-PACK 2MM HM

TYPE M (55 POS.)

PRE-SHIELDED RECEPTACLE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A2 00779	©-352177	—
----------	----------	---

SCALE	NTS	SHEET	1	OF	1	REV	1
-------	-----	-------	---	----	---	-----	---