




SECTION C-C

3.2MAX

1.2MAX

—BODY 0.80±0.03 TONGUE THICKNESS

STAMP : AMP 20-

— $\varnothing 3.68 \pm 0.08$
FOR #6 OR M3.5 STUD

SLEEVE-

INSULATION-

—SERRATIONS

Ø 4.15 MAX

$$\varnothing 7.14 \pm 0.15$$

FOR INSULATION
Ø 1.14 - 2.03

0.79 MIN

6.15 MIN →

17.67 MAX


21.16 MAX

SECTION B - B
SCALE 7:1

MATERIAL & FINISH

SCALE	3.1	SHEET		OF		REV	B
-------	-----	-------	--	----	--	-----	---

mm



MATERIAL	SEE TABLE
----------	-----------

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	$\pm$ -
1 PLC	± 0.3
2 PLC	$\pm$ -
3 PLC	$\pm$ -
4 PLC	$\pm$ -
ANGLES	
FINISH	

SEE TABLE