

M23 P Hood angl. 11-17mm rotatable



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 600 0604
Specification	M23 P Hood angl. 11-17mm rotatable
HARTING eCatalogue	https://b2b.harting.com/09156000604

Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Power
Type of hood/housing	Hood
Description of hood/housing	EMC version Rotatable

Version

Size	M23
Version	Angled entry
Locking type	Screw locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	11 ... 17 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	166.75 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440224 Shell for circular connectors