



SPECIFICATIONS:

METALIZED PLASTIC:
MATERIAL: HIGH TEMPERATURE ABS
PLATING: NICKEL OVER COPPER

PLASTIC:
MATERIAL: HIGH TEMPERATURE ABS
COLOR: BLACK
OPERATING TEMPERATURE: -55°C TO +125°C

BACKSHELL KIT INCLUDES:
(2) BACKSHELL HALVES
(2) 4-40 THUMBSCREWS
(2) HOUSING SCREWS
(1) METAL STRAIN RELIEF CLAMP
(2) STRAIN RELIEF SCREWS

DIMENSIONS					
SIZE	A	B	C	D	E
009	1.240	0.984	1.457	0.598	0.335
015	1.575	1.312	1.457	0.598	0.335
025	2.106	1.852	1.614	0.598	0.433
037	2.756	2.500	1.614	0.598	0.433
050	2.670	2.406	1.614	0.717	0.472



974-YYY-YYYRYY1

SERIES _____
POSITIONS _____
009 _____
015 _____
025 _____
037 _____
050 _____
MATERIAL _____
010 = PLASTIC
020 = METALIZED PLASTIC
COLOR _____
01 = BLACK (ONLY FOR 010 OPTION ABOVE)
12 = NICKEL OVER COPPER (ONLY FOR 020 OPTION ABOVE)
PUT-UPS _____
1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
07/15/2005

UNITS = inch

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
3

DWG NO. 974-YYY-0Y0RYY1