

SHS3 Series

Product selection for die-cast zinc version

Article number	Designation	Switching contact	Max. switching voltage	Type of voltage	Type of connection and direction	Required cable coupling / type	Mounting
					radial	axial	
601.9490.050	SHS3Z-U15Z-KA5 R	2NC/1NO	230 V	AC/DC		Cable	Right
601.9490.051	SHS3Z-U15Z-KA5 L	2NC/1NO	230 V	AC/DC		Cable	Left
601.9490.052	SHS3Z-U15Z-KR5 R	2NC/1NO	230 V	AC/DC	Cable		Right
601.9490.053	SHS3Z-U15Z-KR5 L	2NC/1NO	230 V	AC/DC	Cable		Left
601.9490.054	SHS3Z-U15Z-SA R	2NC/1NO	230 V	AC/DC		M12	Right
601.9490.055	SHS3Z-U15Z-SA L	2NC/1NO	230 V	AC/DC		M12	Left
601.9490.056	SHS3Z-U15Z-SR R	2NC/1NO	230 V	AC/DC	M12		Right
601.9490.063	SHS3Z-U15Z-SR L	2NC/1NO	230 V	AC/DC	M12		Left
601.9490.057	SHS3Z-U1Z-SA R	1NC/1NO	230 V	AC/DC		M12	Right
601.9490.058	SHS3Z-U1Z-SA L	1NC/1NO	230 V	AC/DC		M12	Left
601.9490.059	SHS3Z-U1Z-SR R	1NC/1NO	230 V	AC/DC	M12		Right
601.9490.060	SHS3Z-A2Z-SA R	2NC	230 V	AC/DC		M12	Right
601.9490.061	SHS3Z-A2Z-SA L	2NC	230 V	AC/DC		M12	Left
601.9490.062	SHS3Z-A2Z-SR R	2NC	230 V	AC/DC	M12		Right
601.9490.049	SHS3Z-HINGE						

Product selection for stainless steel version

Article number	Designation	Switching contact	Max. switching voltage	Type of voltage	Type of connection and direction	Required cable coupling / type	Mounting
					radial	axial	
601.9390.023	SHS3-U15Z-KA 5 L	2NC/1NO	230 V	AC/DC		Cable	Left
601.9390.022	SHS3-U15Z-KA 5 R	2NC/1NO	230 V	AC/DC		Cable	Right
601.9390.025	SHS3-U15Z-KR 5 L	2NC/1NO	230 V	AC/DC	Cable		Left
601.9390.024	SHS3-U15Z-KR 5 R	2NC/1NO	230 V	AC/DC	Cable		Right
601.9390.035	SHS3-U15Z-SA L	2NC/1NO	230 V	AC/DC		M12	Left
601.9390.034	SHS3-U15Z-SA R	2NC/1NO	230 V	AC/DC		M12	Right
601.9390.037	SHS3-U15Z-SR L	2NC/1NO	230 V	AC/DC	M12		Left
601.9390.036	SHS3-U15Z-SR R	2NC/1NO	230 V	AC/DC	M12		Right
601.9390.040	SHS3-A2Z-SA-R	2NC	230 V	AC/DC		M12	Right
601.9390.041	SHS3-A2Z-SA-L	2NC	230 V	AC/DC		M12	Left
601.9390.044	SHS3-A2Z-SR-R	2NC	230 V	AC/DC	M12		Right
601.9390.042	SHS3-U1Z-SA-R	1NC/1NO	230 V	AC/DC		M12	Right
601.9390.043	SHS3-U1Z-SA-L	1NC/1NO	230 V	AC/DC		M12	Left
601.9390.045	SHS3-U1Z-SR-R	1NC/1NO	230 V	AC/DC	M12		Right
601.9390.038	SHS3-HINGE (blank hinge)						Both sides

Product selection for stainless steel version in IP 69K

Article number	Designation	Switching contact	Max. switching voltage	Type of voltage	Type of connection and direction	Required cable coupling / type	Mounting
					radial	axial	
6019390064	SHS3-U15Z-KA5-R-IPX	2NC/1NO	230 V	AC/DC		Cable	Right
6019390065	SHS3-U15Z-KA5-L-IPX	2NC/1NO	230 V	AC/DC		Cable	Left
6019390066	SHS3-U15Z-KA5-R-IPX	2NC/1NO	230 V	AC/DC	Cable		Right
6019390067	SHS3-U15Z-KA5-L-IPX	2NC/1NO	230 V	AC/DC	Cable		Left
6019390068	SHS3-7-KA5-IPX/7-KA5-IPX	2 x 1NC/1NO	230 V	AC/DC		Cable	Both sides