




- 注)
NOTE.
- () 内寸法は参考
(DIMENSIONS IN () ARE REFERENCE)
 - 材料 : ナイロン66
MATERIAL : NYLON66

RED	3191-01R1-RE	39-01-9018	94V-2
BLUE	3191-01R1-BU	39-01-9017	94V-2
NATURAL	3191-01R1-201	39-03-6015	94V-0
NATURAL	3191-01R1	39-03-6014	94V-2
色 COLOR	モデル番号 MODEL NO.	POLYBAG PACKAGE	UL
		オーダー番号 ORDER NO.	

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.25
10 OVER 30 UNDER	± 0.3
30 OVER	± 0.35
ANGULAR	± 3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: OBSOLETE PART NUMBERS				molex 1 CKT REC HSG (.093 DIA TERMINAL) PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-3191-003 DOC TYPE PSD DOC PART 001 REVISION M MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL MARKET SHEET NUMBER 1 OF 1	
mm		2:1		EC NO: 650267 DRWN: SKANDB CHK'D: GGA APPR: GGA 2020/10/19 2020/12/10 2020/12/10 INITIAL REVISION: DRWN: K.KOHAMA APPR: M.FUKUSHIMA 2000/03/28 2000/03/31 THIRD ANGLE PROJECTION  DRAWING A3-SIZE SERIES 3191					
GENERAL TOLERANCES (UNLESS SPECIFIED)									
	MM	INCH							
4 PLACES	±								
3 PLACES	±								
2 PLACES	±								
1 PLACE	±								
0 PLACES	±								
ANGULAR TOL ± °									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									