



D Series

AH



HW




Switching Operation

1 NC / 1 NO Contacts


Slow Action

604.1135.019
D-U1 AH



Snap Action

604.1185.173
D-SU1 AH




Slow Action

604.1121.010
D-U1 HW


Snap Action

604.1171.164
D-SU1 HW



2 NC Contacts

604.1835.107
D-A2 AH



-

-

-

2 NO Contacts

614.1835.709
D-E2 AH



-

-


-

1 NC / 1 NO Contacts Overlapping

-

-

604.1321.142
D-UV1Z HW



-

Replacement actuator:

391.4350.924

391.4211.065

Technical Information

Slow Action

Snap Action

Maximum Switching Voltage

240V

240V

Max. Switching Amps (up to)*

10A

10A

B10d (up to)*

20 Million

20 Million

Mechanical Service Life (up to)*

3 x 10⁶

10 x 10⁶

Switching Frequency

≤ 100/min

≤ 100/min

Operating Temperature

-30 °C to +80 °C

-30 °C to +80 °C

Protection Rating

IP65

IP65

Utilization Category (up to)*

AC-15, Ue/Ue 240V 3A

AC-15, Ue/Ue 240V 3A

Rate Insulation Voltage

400VAC

400VAC

Approvals



Special features/variants (on request)

- Available steel with higher temperature range, different lever lengths and additional contacts:
- 3 NC overlapping contact (larger enclosure)
- 2 NC / 2 NO contact (larger enclosure)

- Available steel with higher temperature range, and additional contacts:
- 3 NC overlapping contact (larger enclosure)
- 2 NC / 2 NO contact (larger enclosure)

Drawing dimensions in mm