





Certifications & Ratings

- RoHS compliant

Features & Benefits

- Compatible with automatic placement equipment
- Packaged in 8 mm tape, 7" reel (4000 pcs/reel) and 20 per strip
- Meets EIA-481-1 pkg. std.

Dimensions




Part Number Guide

Part Number										RoHS Compliant	
5	9	9	-	0	2	X	X	-	0	0	X
										F	
Color										Packaging Option	
Red	1	0									2 20 piece tape
Red-Orange	2	0									7 7" reel 4000 pcs/reel
Orange	3	0									
Yellow	4	0									
Yellow-Green	6	0									
Green	8	1									
Blue	9	1									


Tape

Tolerance ± 0.1 mm unless otherwise noted




Reel


Tolerance ± 0.1 mm unless otherwise noted



Soldering





Reflow Profile



Electrical/Optical Characteristics

Electrical/Optical Characteristics					Luminous Intensity		Dominant Wavelength			Forward Voltage		Viewing Angle (°deg.)	Thermal Resistance (°C / W)	Reverse Current Intensity (μA)			
Dialight P/N		Emitted Color	Material	Lens Color	If = 20 ma										Rth(j-s) If=20 ma	(Ir)VR=5V	
20-Piece Tape	7" Reel, 4000 pcs				Min	Typ	Min	Typ	Max	Typ	Max						
599-0210-002F	599-0210-007F	● Red	AlInGaP	Non Diffused	15	29	625	633	640	2.1	2.5	140	450	10			
599-0220-002F	599-0220-007F	● Red-Orange			53	90	620	625	630	2.1	2.5						
599-0230-002F	599-0230-007F	● Orange			68	112	600	605	610	2.1	2.5						
599-0240-002F	599-0240-007F	● Yellow			68	126	585	590	595	2.1	2.5						
599-0260-002F	599-0260-007F	● Yellow-Green			14	54	562	569	575	2.1	2.5						
599-0281-002F	599-0281-007F	● Green	InGaN		195	340	517	525	530	3.2	3.6						
599-0291-002F	599-0291-007F	● Blue			68	105	465	470	475	3.2	3.6						



Absolute Maximum Ratings @ Ts=25 °C

Power Dissipation (mW)	72	105	● G - InGaP ● B
Forward Current (mA)	30		
Reverse Voltage (V)	5		
Operating Temp (°C)	-40 to +100		
Storage Temp (°C)	-40 to +100		
Peak Pulse Fw Current (mA)	60		
Electrostatic Discharge (HBM) (V)	2000	1000	● G - InGaP ● B
Junction Temp (°C)	105		

