




Minimum cable diameter:  
 $\varnothing F_{min}=3,0$

- Maximum cable diameter:
- with rubber bushing:  $\varnothing F_{max}=9,7$
  - without rubber bushing:  $\varnothing F_{max}=12$
  - without reduction plate:  $\varnothing F_{max}=15$

|             |              |
|-------------|--------------|
| 09670500344 | 4-40UNC      |
| Part number | screw thread |

|                                                                                     |  |                                              |  |                                              |  |                           |  |                             |  |                    |  |                                                          |  |             |  |
|-------------------------------------------------------------------------------------|--|----------------------------------------------|--|----------------------------------------------|--|---------------------------|--|-----------------------------|--|--------------------|--|----------------------------------------------------------|--|-------------|--|
|  |  | All Dimensions in mm<br>Original Size DIN A4 |  | Scale<br>1:1                                 |  | Free size tol.            |  | Ref.                        |  |                    |  |                                                          |  |             |  |
|                                                                                     |  |                                              |  |                                              |  |                           |  | Sub.                        |  |                    |  |                                                          |  |             |  |
|  |  | All rights reserved                          |  | Created by<br>DOUGE                          |  | Inspected by<br>BAGDIKIAN |  | Standardisation<br>HOFFMANN |  | Date<br>2013-02-05 |  | State<br>Final Release                                   |  |             |  |
|                                                                                     |  | Department<br>EC PD - FR                     |  | Title<br>D-Sub Hood 50P top entry full metal |  |                           |  |                             |  |                    |  | Doc-Key / ECM-Nr.<br>100521328/UGD/001/A<br>500000056836 |  |             |  |
| HARTING Electronics GmbH<br>D-32339 Espelkamp                                       |  |                                              |  | Type<br>TB                                   |  | Number<br>09670500344     |  |                             |  |                    |  | Rev.<br>A                                                |  | Page<br>1/1 |  |