








(4) 8-32 BINDING
HEAD SCREWS SHIPPED
UNASSEMBLED




6-32 UNC 2B THREADED
MOUNTING HOLE (2 PLCS)



TYCO NO. 1520230-6
(ARAB NO. 8909K500)

90-15569

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WESTEMEIER	01AUG00	TE Connectivity	
		CHK R. WALLEN	02AUG00		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. WALLEN	02AUG00	NAME	20A 250V PANEL MOUNT ROCKER SWITCH
		PRODUCT SPEC			TYCO NO. 1520230-6 (ARAB NO. 8909K500)
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .016 4 PLC ± - ANGLES ± - FINISH	APPLICATION SPEC		SIZE	A1
		WEIGHT		CAGE CODE	00779
MATERIAL				DRAWING NO	1520230
				CUSTOMER DRAWING	
				SCALE	1:1
				SHEET	1 OF 2
				REV	B1



2-1520230-2	7402K4 T-PAK	.469	2.547
2-1520230-1	7402K3 T-PAK	.344	2.422
2-1520230-3	8909K27	.469	2.547
1520230-9	8910K202	.469	2.547
1520230-8	8910K165	.469	2.547
1520230-5	8909K4	.469	2.547
1520230-4	7403K2	.469	2.547
1520230-3	7403K1	.344	2.422
1520230-2	7402K4	.469	2.547
1520230-1	7402K3	.344	2.422
TYCO NO.	ARAB NO.	DIM 'A'	DIM 'B'
		90-347	