





2		1					
LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
		E1		REVISE D PER ECO-11-005294	30APR11	RK	HMR




282858-2 AS SHOWN
SCALE 2:1

- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 WIRE SIZE RANGE
SOLID WIRE: 0,03-4mm² (11AWG).
STRANDED WIRE: 0,03-2,5mm² (13AWG).
- 4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 5 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 6 NOT CUMULATIVE TOLERANCE.



125	13	1-282858-3
115	12	1-282858-2
105	11	1-282858-1
95	10	1-282858-0
85	9	282858-9
75	8	282858-8
65	7	282858-7
55	6	282858-6
45	5	282858-5
35	4	282858-4
25	3	282858-3
15	2	282858-2
DIM. A		N° OF POS. PART NUMBER



		DWN 05SEP2001 E. ZANOLINI		 TE Connectivity											
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 05SEP2001 D. BIEVENOUR		NAME TERMINAL BLOCK, PCB MOUNT, SIDE ENTRY WIRE, 10.0mm PITCH									
mm				APVD 05SEP2001 D. BIEVENOUR											
		0 PLC ±-		PRODUCT SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
		1 PLC ±.3		108-20166		A3		00779		C=282858		-			
		2 PLC ±.25		APPLICATION SPEC											
MATERIAL		4 PLC ±-		114-20079											
ANGLES ±2		FINISH		WEIGHT											
				-		CUSTOMER DRAWING		SCALE		3:1		SHEET 1 OF 1		REV E1	