





LOC		DIST		REV				REVISIONS			
-		-		P		L		DESCRIPTION		DATE	
				E		REV PER RTS-530595-1		12SEP2011		RJM3	
				F		REL. PER ECO-11-018432		12SEP2011		RJM3	
				C		ADDED DASH 2		01JUNE2010		STM	
				D		PART MARKING AND FORMAT UPDATED		24MAR2011		RJM3	

- 1 MATERIAL: SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - BERYLIUM COPPER, ALLOY UNS C17300 CONDITION T004, PER ASTM B196.
INSULATORS - TEFLON (PTFE) ROD, PER ASTM D 1710.
MODULE BODY & OSMC CONNECTORS - STAINLESS STEEL, PER UNS S30300
SLOTTED SPRIN PIN - NICKEL STAINLESS STEEL
- 2 FINISH: MODULE BODY, CONNECTOR BODIES & CENTER CONTACT - GOLD PLATE OVER NICKEL
SLOTTED SPRING PIN - PASSIVATED
- 3 FINISH: MODULE BODY, OSMC CONNECTOR BODY & SLOTTED SPRING PIN - PASSIVATED
SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - GOLD PLATE OVER NICKEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN RJM3	04FEB2011	 TE Connectivity	
DIMENSIONS:		CHK STM	04FEB2011		
INCHES		APVD STM	04FEB2011		
		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT			
		CUSTOMER DRAWING			
		SCALE			
WATERLAL		NAME 8 POSITION P.C.B. MOUNT RF MODULE, OSMM CONTACTS VITA 67 BACKPLANE - C'SINK MTG. HOLES			RESTRICTED TO
		SIZE CAGE CODE DRAWING NO A100779C=1996777			
SEE TABLE		SHEET 1 OF 1			
		REV F			