

2007

RELEASED FOR PUBLICATION


THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT2007




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HJ	-		C1	ECR-14-007162 (Packaging information)	13OCT2015	AP	AK
			C	REVISED PER ECO-13-009645	18JUN2013	UKo	AK
			B3	New HF3 91R, HF3 93R, HF3 96R	12JAN2012	UKo	BK
			B2	Printing, new HF3 53RS	09JUL2010	UKo	HD




Packaging data code (Box, bag, reels):
P(YWWDSL)000
Shipping data code:
YYWW

P - Product code (9 to HF relay)
Y(Y) - Year (last digit for packaging)
WW - calendar week (from date code)
D - Day of the week (1=Sat,.....and 7=Fri)
S - Shift (1=day shift, 2 night shift)
L - Production Line
C - Weekly sequential number
000 - For internal use

Pos.	Relay-Typ	Mark 1)	Mark 2)	PN
1	HF3 51	51	3	1462051-1
2	HF3 51S	51S	3	3-1462051-0
3	HF3 52	52	4.5	1-1462051-6
4	HF3 52S	52S	4.5	2-1462051-8
5	HF3 53	53	5	1462051-2
6	HF3 53RS	53RS	5	3-1462051-3
7	HF3 53S	53S	5	2-1462051-3
8	HF3 54	54	6	1-1462051-7
9	HF3 55	55	9	1462051-3
10	HF3 56	56	12	1462051-4
11	HF3 56S	56S	12	3-1462051-1
12	HF3 57	57	24	1462051-5
13	HF3 57S	57S	24	2-1462051-2
14	HF3 71	71	3	1462051-6
15	HF3 72	72	4.5	1-1462051-8
16	HF3 73	73	5	1462051-7
17	HF3 73S	73S	5	2-1462051-7
18	HF3 74	74	6	1-1462051-9

DIMENSIONS:		DWN	04APR2007	MATERIAL		FINISH									
mm		UKo 9193		-		-									
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	04APR2007	TE Connectivity											
		HD 9121													
		APVD	04APR2007	NAME HF3-Relay 50Ω Marking											
		HD 9121													
		PRODUCT SPEC						SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
-		A4		00779	C- 1462051-1		-								
APPLICATION SPEC		-		CUSTOMER DRAWING				SCALE	5:1	SHEET	1	OF	2	REV	C1
-		WEIGHT		-											
0 PLC ±-															
1 PLC ±-															
2 PLC ±-															
3 PLC ±-															
4 PLC ±-															
ANGLES ±-															
															

2007	RELEASED FOR PUBLICATION	ALL RIGHTS RESERVED.	COPYRIGHT2007	LOC	DIST	REVISIONS					
				HJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
						-	SEE SHEET 1	-	-	-	
Pos.		Relay-Typ	Mark 1)	Mark 2)	PN						
19	HF3 75	75	9	1462051-8							
20	HF3 76	76	12	1462051-9							
21	HF3 77	77	24	1-1462051-0							
22	HF3 91	91	3	1-1462051-1							
23	HF3 91S	91S	3	3-1462051-2							
24	HF3 91R	91R	3	3-1462051-7							
25	HF3 92	92	4.5	2-1462051-0							
26	HF3 92S	92S	4.5	2-1462051-5							
27	HF3 93	93	5	1-1462051-2							
28	HF3 93S	93S	5	2-1462051-4							
29	HF3 93R	93R	5	3-1462051-5							
30	HF3 94	94	6	2-1462051-1							
31	HF3 95	95	9	1-1462051-3							
32	HF3 96	96	12	1-1462051-4							
33	HF3 96S	96S	12	2-1462051-6							
34	HF3 96R	96R	12	3-1462051-6							
35	HF3 97	97	24	1-1462051-5							
DIMENSIONS:		DWN	04APR2007	MATERIAL	FINISH						
mm		UKo 9193		-		-					
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	04APR2007	 TE Connectivity							
		HD 9121									
		APVD	04APR2007	NAME							
		HD 9121									
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC	HF3-Relay 50Ω Marking								
		-									
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO								
		-									
		WEIGHT	-	A4 00779		C- 1462051-1		-			
CUSTOMER DRAWING				SCALE	5:1	SHEET	2	OF 2	REV C1		