




- 103741



|                                                                                       |  |                                           |  |                    |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|-------------------------------------------|--|--------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>L. RINGLEY                         |  | 7-19-85            |  |  TE Connectivity |  |
|                                                                                       |  | CHK<br>R. ELICKER                         |  | 7-19-85            |  |                                                                                                       |  |
| DIMENSIONS:<br>INCHES                                                                 |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |  | APVD<br>R. ELICKER |  | NAME                                                                                                  |  |
|  |  | 0 PLC ± -                                 |  | PRODUCT SPEC       |  | ASSEMBLY, MOD II, HEADER,<br>BREAKAWAY, SINGLE ROW, .100 C/L,<br>VERTICAL, WITH .025 SQ. POSTS        |  |
|                                                                                       |  | 1 PLC ± -                                 |  | —                  |  |                                                                                                       |  |
|                                                                                       |  | 2 PLC ± -                                 |  | APPLICATION SPEC   |  |                                                                                                       |  |
|                                                                                       |  | 3 PLC ± .005                              |  | —                  |  | SIZE                                                                                                  |  |
|                                                                                       |  | 4 PLC ± -                                 |  | WEIGHT             |  | CAGE CODE                                                                                             |  |
|                                                                                       |  | ANGLES                                    |  | —                  |  | DRAWING NO                                                                                            |  |
| MATERIAL                                                                              |  | FINISH                                    |  | A2                 |  | RESTRICTED TO                                                                                         |  |
| PHOSPHOR BRONZE                                                                       |  | SEE TABLE                                 |  | 00779              |  | C-103741                                                                                              |  |
|  |  |                                           |  | CUSTOMER DRAWING   |  | SCALE 4:1                                                                                             |  |
|                                                                                       |  |                                           |  |                    |  | SHEET 1 OF 1                                                                                          |  |
|                                                                                       |  |                                           |  |                    |  | REV H2                                                                                                |  |