

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

FEB ,2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
E	B		D	ECO-09-003420	15 Feb 09	RITA BOB
			E	ECO-12-014680	20Aug2012	TITAN MARTIN

- NOTES:
- 1

SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

50 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3



Au PLATING OVER Ni PLATING OVER Cu PLATING
- 4

Ni PLATING OVER Cu PLATING
- 5

TIN PLATING
- 6

FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 7

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



						Obsolete					
					2		2	BRASS	⚠5	MOUNTING POST	5
					1		1	BRASS	⚠5	SOLDER TAIL	4
					1		1	PE-606		INSULATOR	3
					1		1	ZINC ALLOY	⚠4	BODY	2
					1		1	BRASS	⚠3	CONTACT	1
					6--0		1--0	MATERIAL		DESCRIPTION	ITEM
					⚠2	⚠1					
QUANTITY PER ASSY							PARTS LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH ± -

MATERIAL

SEE TABLE

DWN
RITA ZUO
15 Feb 09

CHK
ANSON MA
15 Feb 09

APVD
BOB ZHAO
15 Feb 09

PRODUCT SPEC
108-112000

APPLICATION SPEC
-

WEIGHT
-

TE Connectivity

NAME
BNC ELBOW PCB SOCKET LOW PROFILE 50 OHM

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1337521

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
E