





FCIconnect.com


Copyright FCI



PART NO: 8614-00-01-1-YD-1-775-LF

ORDERING INFORMATION

SERIES	8614 - 00 - XX - X - YD - 1 - 775-LF	LEAD FREE
OPEN MALE HEADER		SPECIAL CODES
NO: OF CONTACTS		PLATING
01 TO 36 FOR SINGLE ROW		1 - TIN PLATED
02 TO 72 FOR DOUBLE ROW		
NO. OF ROWS		
1 - SINGLE ROW		
2 - DOUBLE ROW		
SPACER TYPE		



Recommended PCB Layout

NOTES

- THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004
- TECHNICAL SPECIFICATION REFER DRAWING : C-8614-0000

mat'l. code				surface		tolerance		projection		product family										
NOTE 2				ISO 1302		ISO 406 ISO 1101				8614										
ltr	ecn no	dr	date	tolerances unless otherwise specified								title								
A	-	GM	2015-01-20	angles	linear	.0±0.1				MM		8614 OPEN HEADER								
						.00±0.2						(SPL. STRAIGHT SOLDER)								
						0°±1°				scale 2:1										
				dr	GREGAR		2015-01-20				dwg no				sheet 1 of 1				size	
				engr	GREGAR		2015-01-20				C-8614-0216				A3					
				chr	GREGAR		2015-01-20													
				appd	BIJU K PAUL		2015-01-20													
sheet index		revision		A							type		Product		Customer		Drawing			
		sheet		1																