



RIGHT ANGLE PLUG CRIMP TYPE FOR FLEXIBLE CABLES




cable	part number	capt. center cont.	assembly	finish	note
10/50 S + D	R185 174 000	yes	M04	Silver+BBR	RG213 & RG 393
11/50 D	R185 177 000	yes	M04		

RIGHT ANGLE PLUG CLAMP TYPE FOR FLEXIBLE CABLES



cable	part number	capt. center cont.	assembly	finish
10 + 11/50 D	R185 160 000	yes	M03	Silver+BBR

RIGHT ANGLE PLUG EZ FIT TYPE FOR CORRUGATED CABLES



cable	part number	dimension			capt. center cont.	assembly	finish
		A	B	C			
1/4" superflexible corrugated	R185 164 200	7.95	4.7	57.9	yes	M02	Silver+BBR
1/2" superflexible corrugated	R185 165 200	14	8.8	57.9	yes	M02	Silver+BBR
3/8" superflexible corrugated	R185 166 200	11	7.1	58.4	yes	M02	

Note : standard packaging = 20 pieces. For unit packaging, add "W" after the P/N.