



	10	9	8	7	6	5	4	3	2	SD-19069-012
	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.003/(0.08)	PACKAGING					
F	191930198	D-356-06	6	.146/(3.71)	LOOSE PIECE					
	191930200	D-356-08	8	.173/(4.39)						
	191930202	D-356-10	10	.198/(5.03)						
	191930204	D-356-14	14	.265/(6.73)						
E	191930199	D-356-06T	6	.146/(3.71)	TAPE					
	191930201	D-356-08T	8	.173/(4.39)						
	191930203	D-356-10T	10	.198/(5.03)						
	191930205	D-356-14T	14	.265/(6.73)						



TAPE MOUNTING LOCATION



SALES DRAWING

NOTES:
1. MATERIAL: COPPER
PLATING: ELECTRO-TIN.
2. BRAZED SEAM.

NEW RELEASE EC NO. ETC2003-0024 DRWN: BRE 02/07/30 CHK: HEB 02/07/30 APPR: RWD 02/07/30 A			DESCRIPTION	QUALITY SYMBOLS MAJOR CRITICAL	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 4:1	DESIGN UNITS ☐ mm ☒ INCH	 THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☒ INCH ☐ mm ONLY		SHT	REV																
													REVISE ON CAD ONLY																
A			REV		<table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>±0.</td><td>±.</td></tr><tr><td>3 PLACES</td><td>±0.</td><td>±.</td></tr><tr><td>2 PLACES</td><td>±0.</td><td>±.</td></tr><tr><td>1 PLACE</td><td>±0.</td><td>±.</td></tr></table>			mm	INCH	4 PLACES	±0.	±.	3 PLACES	±0.	±.	2 PLACES	±0.	±.	1 PLACE	±0.	±.	DRAWN BY & DATE BRE 02/07/23 CHECKED BY & DATE HEB 02/07/23 APPROVED BY & DATE RWD 02/07/23		TITLE: RING TONGUE TERMINAL VERSAKRIMP 8 AWG MOLEX INCORPORATED					
								mm	INCH																				
							4 PLACES	±0.	±.																				
							3 PLACES	±0.	±.																				
2 PLACES	±0.	±.																											
1 PLACE	±0.	±.																											
A			REV		ANGULAR: ±1/2 °		CAD FILENAME		MATERIAL NO.	DRAWING NO.	SHEET NO.																		
							SD-19069-012 .DGN		SEE CHART	SD-19069-012	1 OF 1																		
A			REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						SIZE																
													B																